

Intrinsically Safe Platform Scales

HV-CEP/HW-CEP

Series



IECEx: Ex ia IIB T4 Ga
 ATEX: II 1G Ex ia IIB T4 Ga
 FM/FMc (NEC505): AEx/Ex ia IIB T4
 FM/FMc (NEC500): IS / I / 1 / C,D / T4

**Minimum Investment,
 Maximum Safety!**



A&D ...Clearly a Better Value
 A&D Company, Limited
<http://www.aandd.jp>



Danger Comes When You Least Expect It

Boom! Sparks in potentially explosive atmospheres (like those that arise where petrol and other flammable chemicals are processed) can turn a plant floor into a raging inferno in an instant. If you perform weighing in these types of environments, your equipment must have the proper features to prevent explosions and loss of life.

The HV-CEP/HW-CEP series of internationally certified (i.e. IECEx, ATEX and FM/FMc), intrinsically safe*¹ platform scales will always keep you and your colleagues safe from the risk of these tragedies!

*¹ Limits the energy available to a level insufficient to cause sparks or heat that can ignite flammable gases or vapors

Areas in which the HV-CEP/HW-CEP series is safe for use

	Flammable gases/ vapors present continuously	Flammable gases/ vapors present intermittently	Flammable gases/ vapors present only accidentally
IECEX ATEX FM/FMc (NEC505)	Zone 0	Zone 1	Zone 2
FM/FMc (NEC500)	Division 1		Division 2

You can bring the scale worry-free to locations where ignitable concentrations of flammable gases, vapors or liquids are present continuously or for long periods of time under normal operating conditions (i.e. Zone 0 or Division 1).

Wide selection of capacities and resolutions

Select a scale that best suits your application and budget from either the HV-CEP series of three multi-interval*² models and the HW-CEP series of four high-resolution models (see the specifications for details). All models are offered at affordable prices for intrinsically safe weighing instruments.

*² The lighter the target object, the finer the readability.

IP65 dust & waterproof base unit with stainless steel (SUS430) pan

In addition to being intrinsically safe, the base unit of the HV-CEP/HW-CEP series can be washed with water and can weigh wet objects without problems. Further, the surface of the pan is resistant to chemicals, scratches and rust, and easy to keep clean and hygienic.



IP65 base unit with a SUS430 pan

Multi-colored 5-step LED comparator lights

With the clearly-discernible LED signals, check weighing (judging whether the measured weight is within the designated limits) becomes far more accurate and efficient than with a numeric display alone. Comparisons can be made in three levels, five levels, or even seven levels*³ for both normal weighing and piece counting.

Auto-tare and negative comparison functions

The scale can perform tare*⁴ automatically when the weight reaches the set target range. Additionally, negative values can be used as comparator limits. When these functions are combined, "take-away" check weighing becomes possible; that is, you can measure out a target amount repeatedly from a container without the hassle of pressing the TARE key each time.

*⁴ To offset the weight of the object on the scale and return the display to zero

*³ With no light indicating either end of the continuum



LCD display (25 mm character height) with white backlight

Do not underestimate the effect of display visibility on operator work efficiency, fatigue and tendency to make errors, especially in areas where illumination is not sufficient.

Quick and easy settings using the alphanumeric keypad

Direct alphanumeric input makes it simple and straightforward to enter/re-enter preset tare values, comparator limits, calibration values and various internal settings.

Key lock function

You can inhibit the use of certain keys to prevent operators from making unwanted changes to the scale settings.

Long battery life of approx. 1,500 hours*⁵

The HV-CEP/HW-CEP series operates on 4 D batteries*⁶, making it unnecessary to secure power from a safe area via a safety barrier.

Auto power OFF function

To avoid wasting power, the scale powers off automatically when it is inactive for a set period of time (5 to 60 minutes).

*⁵ With LED and backlight OFF (or approx. 1,000 hours with LED and backlight ON)

*⁶ The batteries to be used are specified: DURACELL MN1300, ENERGIZER E95, or Panasonic LR20 (XJ).

Other Useful Features

- ✓ High-speed measurement—response in 1 second or less (typical for the HV-CEP series) *⁷
- ✓ Five selectable combinations of weighing speed and stability to get the optimal performance under the given environmental conditions
- ✓ Display hold function that makes it easy to read and record the display value when external disturbances can occur unexpectedly
- ✓ Counting mode to count a number of small pieces of the same mass value instantly and precisely
- ✓ Accumulation (M+) function to display the sum total of separate weighing results
- ✓ Display angle adjustable to five levels to suit the convenience of individual operators

*⁷ Time required for the last digit to settle (the stabilization mark will be lit one second after). With the HW-CEP series, response typically takes not more than 1.5 seconds.

Specifications


		HV-15KCEP	HV-60KCEP	HV-200KCEP	HW-10KCEP	HW-60KCEP	HW-100KCEP	HW-200KCEP
kg	Capacity	3 / 6 / 15* ⁱ	15 / 30 / 60* ⁱⁱ	60 / 150 / 220* ⁱⁱ	10	60	100	220
	Min. display	0.001 / 0.002 / 0.005* ⁱ	0.005 / 0.01 / 0.02* ⁱ	0.02 / 0.05 / 0.1* ⁱ	0.001	0.005	0.01	0.02
lb	Capacity	6 / 15 / 30* ⁱ	30 / 60 / 150* ⁱⁱ	150 / 300 / 500* ⁱⁱ	20	150	200	500
	Min. display	0.002 / 0.005 / 0.01* ⁱ	0.01 / 0.02 / 0.05* ⁱ	0.05 / 0.1 / 0.2* ⁱ	0.002	0.01	0.02	0.05
oz	Capacity	96 / 240 / 480* ⁱ	480 / 960 / 2400* ⁱⁱ	2400 / 4800 / 8000* ⁱⁱ	320	2400	3200	8000
	Min. display	0.05 / 0.1 / 0.2* ⁱ	0.2 / 0.5 / 1* ⁱ	1 / 2 / 5* ⁱ	0.05	0.2	0.5	1
lb-oz	Capacity	30 lb	N/A		20 lb	N/A		
	Min. display	0.1 oz	N/A		0.1 oz	N/A		
Counting mode	Max. countable number	150,000	120,000	110,000	100,000	120,000	100,000	110,000
	Number of samples	5, 10, 20, 50 or 100						
Response time* ⁱⁱ	Within 1 second				Within 1.5 seconds			
Repeatability (std. deviation) [kg]	0.001 / 0.002 / 0.005	0.005 / 0.01 / 0.02	0.02 / 0.05 / 0.1	0.002	0.01	0.02	0.04	
Linearity [kg]	±0.001 / ±0.002 / ±0.005	±0.005 / ±0.01 / ±0.02	±0.02 / ±0.05 / ±0.1	±0.002	±0.01	±0.02	±0.04	
Sensitivity drift (typical)	±20 ppm / °C (5 °C to 35 °C / 41 °F to 95 °F)							
Display	7 segment LCD (Character height: 25 mm) with backlight 3-color, 5-step LED comparator lights							
Display refreshment rate	10 times / second							
Operating temperature	-10 °C to 40 °C / 14 °F to 104 °F, 85% R.H. or less (no condensation)							
Power supply	Four D-size, alkaline, 1.5 V batteries * ⁱⁱⁱ							
Battery life (approx.)	1,500 hours with LED and backlight OFF or 1,000 hours with LED and backlight ON							
Weighing pan size	250 × 250 mm	330 × 424 mm	390 × 530 mm	250 × 250 mm	330 × 424 mm	390 × 530 mm		
	9.8 × 9.8 in	13.0 × 16.7 in	15.4 × 20.9 in	9.8 × 9.8 in	13.0 × 16.7 in	15.4 × 20.9 in		
Dimensions (W × D × H)	250 × 439 × 397 mm	330 × 585 × 776 mm	390 × 691 × 776 mm	250 × 439 × 397 mm	330 × 585 × 776 mm	390 × 691 × 776 mm		
	9.8 × 17.3 × 15.6 in	13.0 × 23.0 × 30.6 in	15.4 × 27.2 × 30.6 in	9.8 × 17.3 × 15.6 in	13.0 × 23.0 × 30.6 in	15.4 × 27.2 × 30.6 in		
Weight (approx.)	8 kg / 17.6 lb	12 kg / 26.5 lb	18 kg / 39.7 lb	8 kg / 17.6 lb	12 kg / 26.5 lb	18 kg / 39.7 lb		

*ⁱ Multi-interval: The lighter the target object, the finer the readability.

*ⁱⁱ Time required for the last digit to settle (the stabilization mark will be lit one second after), which is subject to the weighing environment, response characteristic setting and how the target object is placed.

*ⁱⁱⁱ Only DURACELL MN1300, ENERGIZER E95, or Panasonic LR20 (X) can be used (but not mixed).

Dimensions (mm/inches)



Platform only

A&D

...Clearly a Better Value

A&D Company, Limited

3-23-14 Higashi-Ikebukuro, Toshima-ku, Tokyo 170-0013 JAPAN
Telephone:[81](3) 5391-6132 Fax:[81](3) 5391-1566
http://www.aandd.jp

A&D ENGINEERING, INC.

1756 Automation Parkway, San Jose, CA 95131 U.S.A.
Telephone:[1](408) 263-5333 Fax:[1](408) 263-0119

A&D Australasia Pty Ltd.

32 Dew Street, Thebarton, South Australia 5031 AUSTRALIA
Telephone:[61](8) 8301-8100 Fax:[61](8) 8352-7409

A&D INSTRUMENTS LTD.

Unit 24/26 Blacklands Way Abingdon Business Park,
Abingdon, Oxon OX14 1DY UNITED KINGDOM
Telephone:[44](1235) 550420 Fax:[44](1235) 550485

<German Sales Office>

Hamburger Straße 30 D-22926 Ahrensburg GERMANY
Telephone:[49](0) 4102 459230 Fax:[49](0) 4102 459231

A&D KOREA Limited

817, Manhattan Bldg., 33, Gukjegeumyung-ro 6-gil,
Yeongdeungpo-gu, Seoul, 07331, KOREA
Telephone:[82](2) 780-4101 Fax:[82](2) 782-4280

A&D RUS CO., LTD.

Vereyskaya str.17, Moscow, 121357 RUSSIA
Telephone: [7] (495) 937-33-44 Fax: [7] (495) 937-55-66

A&D Instruments India Private Limited

509 Udyog Vihar Phase V
Gurgaon-122 016, Haryana, INDIA
Telephone: [91](124) 471-5555 Fax: [91](124) 471-5599