

	CODE	IMAGE	DESCRIZIONE - DESCRIPTION - DESCRIPTION - BESCHREIBUNG - DESCRIPCIÓN
OPTIONAL	LEVIGAT.PNEU		Fino a 2 utensili in contemporanea - Up to 2 tools at the same time Jusq'à 2 ponçouses au même temp - Bis zum 2 Gerät gleichzeitig - Hasta 2 lijadoras en simultáneo
	GINGO-YA		Biforcazione Ø 32 mm - Two-way deviation Ø 32 mm - Déviation Ø 32 mm - Desviación en Y Ø 32 mm - Abzweigung Ø 32 mm
	GINGO-YP		Raccordo doppio pneumatico - Fitting double tires - Pneus doubles montage - Fitting Doppelbereifung - Neumáticos dobles de montaje
RICAMBI - SPARE PARTS	GINGO-CART		Filtro a cartuccia in cellulosa H265 Ø218 - Cartridge filter in cellulose H265 Ø218 - Filtre à cartouche dans la cellulose H265 Ø218 - Patronenfilter im Zellstoff H265 Ø218 - Filtro de cartucho en H265 celulosa Ø218

Manichette - Hoses - Tuyaux - Schläuche - Mangueras

CODE	IMAGE	(Ø)	(m)	Attacco (Ø)	Tipo circuito	(V)	presa	GINGO-YA
AC/83-S		38/29	3	50	aria	-		-
AC/82		38/29	6	50				-
AC/88		32	3	32				√
AC/89		32	6	32				√
AC/87-R		38/29	3	50	elettrica	230	SHUKO	-
AC/84-T		38/29	6	50				-
AC/90-T		32	3	32				√
AC/91-T		32	6	32				√



Esempio di GINGO da impianto.
Example GINGO implant.
Exemple GINGO implant.
Beispiel GINGO Implantat.
Implante Ejemplo GINGO.



Esempio di GINGO versione standard.
Example GINGO standard version.
Exemple GINGO version standard.
Beispiel GINGO Standardversion.
Ejemplo GINGO versión estándar.

